



Bench grinder DS with dust extraction, 400 V, Type: DS15/300A



Order data

Order number	077514 DS15/300A
GTIN	2050001674135
Item class	03S

Description

Version:

Double-ended bench grinding machine with extraction system incorporated in the base. Grinding dust is effectively collected by a water filter and downstream plastic coarse filter and fine filter. **Supplied without grinding wheels.**

Note:

Suitable grinding wheels can be found from No. 596100.

Power consumption: 1100 W

maximum speed: 1450 min⁻¹

Abrasive disc Ø D: 300 mm

Abrasive disc width T: 40 mm

Abrasive disc hole Ø H: 76 mm

Extraction conveying volume: 10 m³/min

Technical description

maximum speed	1450 min ⁻¹
Manufacturer's designation	DS15/300A

Power consumption	1100 W
Weight	160 kg
Extraction conveying volume	10 m ³ /min
Abrasive disc width T	40 mm
Abrasive disc hole Ø H	76 mm
Abrasive disc Ø D	300 mm
Power supply	Mains operated
Type of product	Double grinding machine

Accessories

Bench grinding wheel D×T×H (mm) Type EK60	596610 EK60
Bench grinding wheel D×T×H (mm) Type SC80	596610 SC80
Bench grinding wheel D×T×H (mm) Type NK60	596610 NK60
Bench grinding wheel D×T×H (mm) Type NK24	596610 NK24