

**DNMG 150608, Grade: PV720****Order data**

Order number	250797 PV720
GTIN	4960664724611
Item class	25E

Description

DNMG 150608 PV720 Grade: PV720

Chip breaker: PG

Cutting depth a_p : 1 - 4 mm

Feed f : 0.15 - 0.6 mm/rev.

Cutting speed v_c main application: 110 - 490 m/min

Technical description

Cutting depth a_p	1 - 4 mm
Corner radius	0.8 mm
Grade	PV720
Cutting conditions	continuous
Chip breaker	PG
Main application	P
Cutting speed v_c main application	110 - 490 m/min

Feed f	0.15 - 0.6 mm/rev.
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Cermet
ISO code indexable insert	DNMG 150608
Number of changes/inserts	4
Type of product	Indexable insert for turning