



Precision small dial indicator shock-resistant, Measuring range / Body Ø: 5/40mm



Order data

Order number	432550 5/40
GTIN	4031452101560
Item class	46C

Description

Version:

Precision small dial indicators with strong metal casing, clamping shank \varnothing 8 mm h6, hardened and ground. Outer ring of dial face can be rotated to zero the dial.

Shock-resistant.

Dimensions to DIN EN ISO 463, issue June 2006.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Technical description

Calibration	C1
Graduation	0.01 mm
Gauging force	1 - 1.4 N
Measuring range	5 mm
Body \varnothing	40 mm

Reading per pointer revolution	0.5 mm
Standard	DIN 878
Measurement variation MPE (measurement range)	12 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5
Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023000 10

Accessories

Dial indicator glass Type 40	432010 40
Steel contact point Type 13	434900 13
Steel contact point Type 15	434900 15
Steel contact point Type 14/30	434900 14/30
Steel contact point Type 18/1	434900 18/1
Carbide contact point Type 18/1	434910 18/1
Steel contact point Type 14/20	434900 14/20
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 14	434900 14
Steel contact point Type 20	434900 20
Carbide contact point Type 18/3	434910 18/3
Carbide contact point Type 18/5	434910 18/5
Steel contact point Type 11/25	434900 11/25
Steel contact point Type 30/10	434900 30/10
Carbide contact point Type 11	434910 11

Carbide contact point Type 10	434910 10
Steel contact point Type 14/15	434900 14/15
Carbide contact point Type 14	434910 14
Steel contact point Type 11	434900 11
Steel contact point Type 11/15	434900 11/15
Steel contact point Type 28	434900 28
Steel contact point Type 14/40	434900 14/40
Carbide contact point Type 18/2	434910 18/2
Carbide contact point Type 16	434910 16
Steel contact point Type 18/3	434900 18/3
Steel contact point Type 11/35	434900 11/35
Steel contact point Type 10	434900 10
Carbide contact point Type 17	434910 17
Angled bracket for dial indicator 45° Clamping length 50 mm	434917 50
Steel contact point Type 18/6	434900 18/6
Extension for contact points Length L 100 mm	434920 100
Carbide contact point Type 18/6	434910 18/6
Steel contact point Type 18/4	434900 18/4
Steel contact point Type 12	434900 12
Extension for contact points Length L 15 mm	434920 15
Extension for contact points Length L 30 mm	434920 30
Extension for contact points Length L 90 mm	434920 90
Carbide contact point Type 18/4	434910 18/4
Extension for contact points Length L 10 mm	434920 10
Steel contact point Type 29/20	434900 29/20
Angled bracket for dial indicator 60° Clamping length 50 mm	434918 50
Steel contact point Type 2	434900 2
Steel contact point Type 29/10	434900 29/10

Steel contact point Type 11/20	434900 11/20
Steel contact point Type 39	434900 39
Steel contact point Type 24	434900 24
Carbide contact point Type 2	434910 2
Extension for contact points Length L 80 mm	434920 80
Angled bracket for dial indicator 45° Clamping length 25 mm	434917 25
Steel contact point Type 18/5	434900 18/5
Magnetic rear panel for dial indicators for body Ø 40 mm	434835 40
Steel contact point Type 16	434900 16
Angled bracket for dial indicator 60° Clamping length 25 mm	434918 25
Pivoting contact point	434912
Steel contact point Type 17	434900 17
Steel contact point Type 11/30	434900 11/30
Extension for contact points Length L 60 mm	434920 60
Extension for contact points Length L 40 mm	434920 40
Outer ring for dial indicator Type 40	432020 40
Extension for contact points Length L 70 mm	434920 70
Extension for contact points Length L 20 mm	434920 20
Ruby contact point Type 2	434915 2
Extension for contact points Length L 50 mm	434920 50