



## Dial indicator shock-resistant, Measuring range / Body Ø: 10/58 mm



### Order data

Order number	432000 10/58
GTIN	4045197204189
Item class	42C

### Description

#### Version:

Dimensions to DIN EN ISO 463, issue June 2006. **Shock-resistant** precision dial indicators. Clamping shank Ø 8 mm h6, hardened and ground. Outer ring of dial face can be rotated to zero the dial. Outer ring with 2 adjustable tolerance pointers. Central pointer for 1/100 mm reading, small pointer on sub-scale for 1 mm reading.

**Shock-resistant by gear rack sleeve. Full metal version** with plastic dial glass.

#### Standard:

**Shock-resistant** precision dial indicators. Clamping shank Ø 8 mm h6, hardened and ground. Outer ring of dial face can be rotated to zero the dial. Outer ring with 2 adjustable tolerance pointers. Central pointer for 1/100 mm reading, small pointer on sub-scale for 1 mm reading.

#### Optional extras:

Special contact points No. 434900; 434910; 434915.

Packaging: sturdy box

Standard: DIN 878

Calibration: C1

Graduation: 0.01 mm

Reading per pointer revolution: 1 mm

Gauging force: 0.7 - 1.5 N

## Technical description

Gauging force	0.7 - 1.5 N
Calibration	C1
Graduation	0.01 mm
Body Ø	58 mm
Reading per pointer revolution	1 mm
Measuring range	10 mm
Standard	DIN 878
Rotatable dial face	yes
adjustable tolerance marks	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	Dial Indicator

## Services

Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	013210 10
Labelling laser-etched Type	018940
DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	013250 12,5
Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023000 10
DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5

## Accessories

Extension for measuring probe Length L 10 mm	434920 10
Carbide contact point Type 18/1	434910 18/1
Steel contact point Type 14/30	434900 14/30
	434917 50

Angled bracket for dial indicator 45° Clamping length 50 mm

Steel contact point Type 11/30	434900 11/30
Steel contact point Type 14/40	434900 14/40
Steel contact point Type 15	434900 15
Steel contact point Type 16	434900 16
Extension for measuring probe Length L 30 mm	434920 30
Steel contact point Type 11/25	434900 11/25
Steel contact point Type 14	434900 14
Steel contact point Type 29/10	434900 29/10
Steel contact point Type 11/35	434900 11/35
Carbide contact point Type 14	434910 14
Extension for measuring probe Length L 80 mm	434920 80
Steel contact point Type 14/20	434900 14/20
Steel contact point Type 24	434900 24
Ruby contact point Type 2	434915 2
Steel contact point Type 18/5	434900 18/5
Carbide contact point Type 18/2	434910 18/2
Steel contact point Type 18/3	434900 18/3
Carbide contact point Type 11	434910 11
Extension for measuring probe Length L 20 mm	434920 20
Steel contact point Type 39	434900 39
Extension for measuring probe Length L 70 mm	434920 70
Steel contact point Type 12	434900 12
Carbide contact point Type 18/3	434910 18/3
Steel contact point Type 13	434900 13
Extension for measuring probe Length L 60 mm	434920 60
Carbide contact point Type 17	434910 17
Steel contact point Type 30/10	434900 30/10
Carbide contact point Type 18/6	434910 18/6

Steel contact point Type 20	434900 20
Steel contact point Type 18/4	434900 18/4
Carbide contact point Type 16	434910 16
Angled bracket for dial indicator 60° Clamping length 25 mm	434918 25
Steel contact point Type 11/20	434900 11/20
Carbide contact point Type 10	434910 10
Steel contact point Type 11	434900 11
Steel contact point Type 2	434900 2
Angled bracket for dial indicator 60° Clamping length 50 mm	434918 50
Steel contact point Type 29/20	434900 29/20
Extension for measuring probe Length L 50 mm	434920 50
Extension for measuring probe Length L 90 mm	434920 90
Steel contact point Type 17	434900 17
Extension for measuring probe Length L 15 mm	434920 15
Extension for measuring probe Length L 100 mm	434920 100
Extension for measuring probe Length L 40 mm	434920 40
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 28	434900 28
Carbide contact point Type 18/5	434910 18/5
Steel contact point Type 11/15	434900 11/15
Steel contact point Type 14/15	434900 14/15
Carbide contact point Type 18/4	434910 18/4
Steel contact point Type 18/1	434900 18/1
Steel contact point Type 10	434900 10
Steel contact point Type 18/6	434900 18/6
Angled bracket for dial indicator 45° Clamping length 25 mm	434917 25
Carbide contact point Type 2	434910 2

Pivoting contact point	434912
Dial indicator glass Type 58	432260 58