


WN.G 080408, Grade: PV720


Order data

Order number	252114 PV720
GTIN	4960664726684
Item class	25E

Technical description

Chip breaker	PG
Main application	P
Cutting depth a_p	1 - 3.8 mm
Feed f	0.15 - 0.6 mm/rev.
Grade	PV720
Corner radius	0.8 mm
Cutting speed v_c main application	110 - 490 m/min
Cutting conditions	continuous
Finishing/roughing assignment	Semi-roughing
Tool material	Cermet
ISO code indexable insert	WNMG 080408
Number of changes/inserts	6

Tolerance	M
Type of product	Indexable insert for turning