


SNMG 120408, Grade: PV720

Order data

Order number	251164 PV720
GTIN	4960664724758
Item class	25E

Technical description

Corner radius	0.8 mm
Feed f	0.05 - 0.3 mm/rev.
Chip breaker	PQ
Main application	P
Cutting depth a_p	0.2 - 2.5 mm
Grade	PV720
Cutting conditions	continuous
Cutting speed v_c main application	110 - 520 m/min
Finishing/roughing assignment	Finishing
Tool material	Cermet
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8

Type of product

Indexable insert for turning