


TNMG 160404, Grade: PV720

Order data

Order number	251472 PV720
GTIN	4960664725397
Item class	25E

Technical description

Chip breaker	PQ
Corner radius	0.4 mm
Cutting speed v_c main application	110 - 520 m/min
Cutting depth a_p	0.2 - 2.5 mm
Grade	PV720
Feed f	0.05 - 0.3 mm/rev.
Cutting conditions	continuous
Main application	P
Finishing/roughing assignment	Finishing
Tool material	Cermet
ISO code indexable insert	TNMG 160404
Number of changes/inserts	6

Type of product

Indexable insert for turning