

**CCMT 060202, Grade: PV720**

Order data

Order number	260190 PV720
GTIN	4960664726820
Item class	25E

Technical description

Chip breaker	GK
Cutting depth a_p	0.5 - 3 mm
Feed f	0.1 - 0.3 mm/rev.
Cutting conditions	continuous
Main application	P
Corner radius	0.2 mm
Cutting speed v_c main application	60 - 270 m/min
Grade	PV720
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Cermet
ISO code indexable insert	CCMT 060202
Number of changes/inserts	2

Tolerance

M

Type of product

Indexable insert for turning