

Garant
Precision dial indicator shock-resistant, Measuring range / Body Ø: 1/58mm


Order data

Order number	433090 1/58
GTIN	4045197422071
Item class	41C

Description

Version:

Strong, satin chrome plated brass casing; unbreakable dial glass.

Clamping shank Ø 8 mm h6, hardened and ground.

High accuracy version.

The most important parts of the mechanism are **jewel-mounted**.

Central pointer **for 1/1000 mm reading**.

Outer ring of dial face can be rotated to zero the dial.

Nearly constant measuring force over the entire measuring range.

High-quality shock absorption for particularly long working life.

Dimensions to DIN EN ISO 463, issue June 2006.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Technical description

Reading per pointer revolution	0.2 mm
Calibration	C2

Gauging force	1.5 - 2 N
Body Ø	58 mm
Graduation	0.001 mm
Measuring range	1 mm
Standard	Manufacturer's standard
Measurement variation MPE (measurement range)	5 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

CalibrationDial indicator, analogue 0.001 maximum measuring span 5 mm	023020 5
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5

Accessories

Steel contact point Type 11/25	434900 11/25
Carbide contact point Type 10	434910 10
Steel contact point Type 14/15	434900 14/15
Steel contact point Type 17	434900 17
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 20	434900 20
Carbide contact point Type 11	434910 11
Steel contact point Type 18/6	434900 18/6
Carbide contact point Type 18/3	434910 18/3
Extension for contact points Length L 50 mm	434920 50
Angled bracket for dial indicator60° Clamping length 25 mm	434918 25
Steel contact point Type 14/30	434900 14/30

Extension for contact points Length L 80 mm	434920 80
Carbide contact point Type 2	434910 2
Angled bracket for dial indicator 60° Clamping length 50 mm	434918 50
Carbide contact point Type 18/1	434910 18/1
Steel contact point Type 2	434900 2
Steel contact point Type 29/20	434900 29/20
Carbide contact point Type 14	434910 14
Carbide contact point Type 16	434910 16
Steel contact point Type 11/35	434900 11/35
Steel contact point Type 14	434900 14
Carbide contact point Type 18/6	434910 18/6
Steel contact point Type 30/10	434900 30/10
Steel contact point Type 29/10	434900 29/10
Steel contact point Type 15	434900 15
Steel contact point Type 18/1	434900 18/1
Steel contact point Type 13	434900 13
Steel contact point Type 18/5	434900 18/5
Steel contact point Type 11/30	434900 11/30
Extension for contact points Length L 15 mm	434920 15
Steel contact point Type 14/20	434900 14/20
Carbide contact point Type 18/2	434910 18/2
Angled bracket for dial indicator 45° Clamping length 50 mm	434917 50
Extension for contact points Length L 20 mm	434920 20
Steel contact point Type 14/40	434900 14/40
Steel contact point Type 11/15	434900 11/15
Extension for contact points Length L 90 mm	434920 90
Steel contact point Type 24	434900 24
Carbide contact point Type 18/5	434910 18/5

Steel contact point Type 11/20	434900 11/20
Steel contact point Type 28	434900 28
Steel contact point Type 39	434900 39
Pivoting contact point	434912
Extension for contact points Length L 30 mm	434920 30
Carbide contact point Type 17	434910 17
Angled bracket for dial indicator 45° Clamping length 25 mm	434917 25
Carbide contact point Type 18/4	434910 18/4
Ruby contact point Type 2	434915 2
Steel contact point Type 18/4	434900 18/4
Extension for contact points Length L 70 mm	434920 70
Steel contact point Type 12	434900 12
Extension for contact points Length L 60 mm	434920 60
Steel contact point Type 11	434900 11
Steel contact point Type 10	434900 10
Extension for contact points Length L 10 mm	434920 10
Extension for contact points Length L 100 mm	434920 100
Steel contact point Type 16	434900 16
Extension for contact points Length L 40 mm	434920 40
Steel contact point Type 18/3	434900 18/3