




Grinding and inspection vice without spindle, Jaw width A: 65mm



Order data

Order number	363650 65
GTIN	4045197313614
Item class	38F

Description

Version:

- **Hardened steel; precision ground all round.**

Working on 4 different faces (front, rear, and side faces).

Movable jaw can be slid to the component by hand and clamped. **On release, the movable jaw automatically backs away from the component.**

Function:

Pull-down system – The movable jaw is pulled down by the resulting clamping force; no lifting of the component or vibration during machining.

Application:

For **machining and inspection true to gauge.**

Accuracy:

Within **0.003 mm** / 100 mm (system accuracy).

Technical description

Overall length a	230 mm
Weight	4.3 kg
maximum clamping range b	130 mm
Jaw width A	65 mm
Jaw height C	37 mm
Overall width B	65 mm

Type of product

Checking vice