



Precision large dial indicator shock-resistant, Measuring range / Body Ø: 10/100mm



Order data

Order number	432900 10/100
GTIN	4031452100419
Item class	46C

Description

Version:

Dimensions to DIN EN ISO 463, issue June 2006. With larger external dial Ø and extra large graduations, **shock-resistant mechanism**. Satin chrome-plated brass housing. With clamping shank Ø 8 mm h6; hardened and ground. Outer ring of dial face can be rotated to zero the dial. Outer ring with 2 adjustable tolerance pointers. Central pointer for 1/100 mm reading, small pointer on sub-scale for 1 mm reading.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Technical description

Gauging force	1 - 1.8 N
Reading per pointer revolution	1 mm
Body Ø	100 mm
Graduation	0.01 mm

Calibration	C1
Measuring range	10 mm
Standard	Manufacturer's standard
Measurement variation MPE (measurement range)	17 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5
CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023000 10

Accessories

Carbide contact point Type 10	434910 10
Extension for contact points Length L 70 mm	434920 70
Steel contact point Type 29/20	434900 29/20
Carbide contact point Type 18/3	434910 18/3
Angled bracket for dial indicator45° Clamping length 25 mm	434917 25
Extension for contact points Length L 60 mm	434920 60
Carbide contact point Type 17	434910 17
Extension for contact points Length L 100 mm	434920 100
Steel contact point Type 18/1	434900 18/1
Carbide contact point Type 18/2	434910 18/2
Steel contact point Type 18/5	434900 18/5
Carbide contact point Type 18/6	434910 18/6
Steel contact point Type 2	434900 2
Steel contact point Type 15	434900 15

Steel contact point Type 30/10	434900 30/10
Steel contact point Type 11/30	434900 11/30
Steel contact point Type 18/3	434900 18/3
Angled bracket for dial indicator 45° Clamping length 50 mm	434917 50
Steel contact point Type 14/15	434900 14/15
Carbide contact point Type 2	434910 2
Steel contact point Type 11/25	434900 11/25
Ruby contact point Type 2	434915 2
Pivoting contact point	434912
Steel contact point Type 10	434900 10
Steel contact point Type 11/15	434900 11/15
Steel contact point Type 24	434900 24
Carbide contact point Type 18/5	434910 18/5
Extension for contact points Length L 20 mm	434920 20
Steel contact point Type 12	434900 12
Steel contact point Type 16	434900 16
Extension for contact points Length L 10 mm	434920 10
Steel contact point Type 17	434900 17
Steel contact point Type 13	434900 13
Steel contact point Type 11/35	434900 11/35
Carbide contact point Type 18/1	434910 18/1
Extension for contact points Length L 15 mm	434920 15
Angled bracket for dial indicator 60° Clamping length 50 mm	434918 50
Extension for contact points Length L 50 mm	434920 50
Steel contact point Type 14/20	434900 14/20
Steel contact point Type 39	434900 39
Steel contact point Type 28	434900 28
Extension for contact points Length L 30 mm	434920 30

Steel contact point Type 18/6	434900 18/6
Carbide contact point Type 18/4	434910 18/4
Carbide contact point Type 14	434910 14
Carbide contact point Type 16	434910 16
Carbide contact point Type 11	434910 11
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 11	434900 11
Extension for contact points Length L 40 mm	434920 40
Steel contact point Type 11/20	434900 11/20
Steel contact point Type 14	434900 14
Extension for contact points Length L 80 mm	434920 80
Steel contact point Type 14/30	434900 14/30
Steel contact point Type 20	434900 20
Extension for contact points Length L 90 mm	434920 90
Steel contact point Type 18/4	434900 18/4
Angled bracket for dial indicator 60° Clamping length 25 mm	434918 25
Steel contact point Type 29/10	434900 29/10
Steel contact point Type 14/40	434900 14/40