

FLEX**Fillet weld grinder base unit, Type: LLK1503****Order data**

Order number	077770 LLK1503
GTIN	4030293115583
Item class	03S

Description**Version:**

Powerful TRINOXFLEX 18 V cordless motor for metal surface preparation.

- **Heavy-duty brushless motor with higher efficiency.**
- **Unique tool attachment with quick-release coupling for changing (without tools) the four modular attachments for burnishing and pipe finishing, for grinding with belt file or fillet weld grinder.**

Supplied with:

Version without attachment, supplied with 2 × rechargeable batteries 18 V / 5.0 Ah, charger and L-Boxx® 238.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

Suitable grinding wheels can be found under No. 566994 and No. 566996.

Packaging: Modular case (L-Boxx)

Power consumption: 1200 W

maximum speed: 1500 - 4700 rpm

maximum disc Ø: 152 mm

Weight: 3.4 kg

Technical description

Weight	3.4 kg
maximum disc Ø	152 mm
maximum speed	1500 - 4700 rpm
Power consumption	1200 W
Manufacturer's designation	LLK1503
Power supply	Mains operated
Packaging	Modular case (L-Boxx)
Type of product	Fillet weld grinder

Accessories

Compact disc RC-UW Rapid Cut W × D × H (mm) Grit equivalent 50	566994 50
Compact disc D × T × H (mm, see drawing) Grit equivalent 280	566996 280
Compact disc D × T × H (mm, see drawing) Grit equivalent 180	566996 180
Compact disc RC-UW Rapid Cut W × D × H (mm) Grit equivalent 100	566994 100
Clamping nut M14 Type FIXTEC	073930 FIXTEC