


**DCMT 070202, Grade: PV720**

**Order data**

Order number	260481 PV720
GTIN	4960664726868
Item class	25E

**Technical description**

Cutting speed $v_c$ main application	60 - 270 m/min
Corner radius	0.2 mm
Main application	P
Chip breaker	GK
Grade	PV720
Feed $f$	0.1 - 0.3 mm/rev.
Cutting depth $a_p$	0.5 - 3 mm
Cutting conditions	continuous
Finishing/roughing assignment	Semi-roughing
Tool material	Cermet
ISO code indexable insert	DCMT 070202
Number of changes/inserts	2

Tolerance	M
Type of product	Indexable insert for turning