


DC.T 11T308, Grade: PV720

Order data

Order number	260492 PV720
GTIN	4960664726851
Item class	25E

Technical description

Corner radius	0.8 mm
Grade	PV720
Main application	P
Chip breaker	GK
Cutting conditions	continuous
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.5 - 3 mm
Cutting speed v_c main application	60 - 270 m/min
Finishing/roughing assignment	Semi-roughing
Tool material	Cermet
ISO code indexable insert	DCMT 11T308
Number of changes/inserts	2

Tolerance	M
Type of product	Indexable insert for turning