

**VBMT 160408, Grade: PV720****Order data**

Order number	261184 PV720
GTIN	4960664726141
Item class	25E

Technical description

Main application	P
Corner radius	0.8 mm
Chip breaker	HQ
Cutting depth a_p	0.5 - 2 mm
Cutting speed v_c main application	60 - 270 m/min
Cutting conditions	continuous
Grade	PV720
Feed f	0.05 - 0.25 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Cermet
ISO code indexable insert	VBMT 160408
Number of changes/inserts	2

Type of product

Indexable insert for turning