



High-performance cutting oil chlorine-free Alpha 93, Contents: 20l



Order data

| | |
|--------------|---------------|
| Order number | 084210 20 |
| GTIN | 2050000971884 |
| Item class | 08J |

Description

Version:

Cutting oil for the most demanding applications. Recommended for mixing with normal mineral-based cutting oil (but not with water-soluble oils).

Application by brush, spray can, spray bottle or lubrication system.

Advantage:

Improves **tool-life, cutting performance** and **surface quality**. **Chlorine-free** - releases no hazardous vapours, **non-polluting**.

Application:

Multi-purpose for **all machining operations** (turning, milling, drilling, tapping, reaming, broaching and sawing) and also for **forming**. Indispensable when cutting **difficult materials** such as stainless and heat-resistant steels, nickel alloys, titanium, and similar alloys. Ideal for **non-ferrous metals**.

Ideal when minimum lubrication is required, due to being free of mineral oil.

Technical description

| | |
|---------------------|-----------------------|
| Kinematic viscosity | 30 mm ² /s |
| Version | Can |

| | |
|---------------------|----------------------------|
| Flashpoint | > 180 °C |
| Colour | amber colours |
| Storage temperature | 5 - 40 °C |
| Contents | 20 l |
| Type of product | Cutting oil / grinding oil |