



## Non-contact voltage testers



### Order data

Order number	473010
GTIN	4045197554239
Item class	42I

### Description

#### Version:

Compact two-component plastic casing with integral LED torch. Prods with visual indication of voltage by colour change (green to red) and additional acoustic signal. Easily transported, fits any pocket.

#### Function:

IP40: Protected against penetration by foreign bodies with  $\varnothing > 1$  mm, however tools and wires should be kept away, and offers no protection against water.

#### Application:

For non-contact detection of live conductors, e.g. in cables, sockets, junction boxes etc.

#### Standard:

**IEC/EN 61010-1.**

#### Supplied with:

2 batteries No. 081551 size LR3.

### Technical description

Display range AC	50 - 1000 V
IP Index of Protection	IP 40
Overvoltage category	CAT IV / 1000 V
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Type of product	Voltage tester

---

## Accessories

Alkaline-manganese batteries International size LR3

081561 LR3