



TESA MICRO-HITE digital height gauge including control panel, Type: 600



Order data

Order number	445285 600
GTIN	7630041129908
Item class	45B

Description

Version:

Hybrid control panel

- **Backlit keyboard with clear simplified presentation and clear information.**
- **Convenient and flexible operation with parallel use of the keyboard and touch display.**
- **Ergonomic posture due to flexible adjustment of the control panel.**
- **Saves time and simplifies processes for serial measurements.**
- **Optional data management using Stat-Express or Data-Direct measurement software.**
Data can be archived to a USB stick.

TESA MICRO-HITE manually adjustable digital height gauge for comprehensive measurements in 1D or 2D coordinate measuring systems.

- **Incrementally graduated glass scale with reference point.**
- **Automatic correction of systematic measurement variations ensures very high accuracy.**
Coefficient of linear expansion equals that of steel.
- **Switchable air support cushion**
- **User-friendly with multi-lingual context help in the active functions.**

Software / measuring functions

- **Comprehensive measurement facilities such as parallelism, angular measurements, simple 2D measurements, etc.**
- **Integral computer.**

- **Automatic calculation of measurement results by repeated use of programs stored as functions.**
- **Input facility for customer-specific tolerances. ISO tolerances are automatically incorporated in the software. Direct and clear information to the user regarding OK/reject.**
- **Easy generation of test reports.**

Advantage:

Significantly faster measurement of the return points (min, max, Ø) by use of the patented Quick-Center technology. All measurements shown visually for information in noisy environments.

Application:

Thanks to the sturdy construction, suitable for workshop use as well as for laboratory applications. Ideal for series measurements.

Supplied with:

TESA MICRO-HITE base unit incl. control panel, standard contact point carrier, standard contact point with contact rod and 5 mm Ø measurement ball, reference piece, electric pump (fitted) for air pad for the gauge base, battery cartridge (rechargeable Lithium-ion battery), mains adaptor (charger), mains cable. **SCS calibration certificate.**

Optional extras:

USB printer No. 445293; printer paper No. 445294; data cable No. 498918 size USB; Data-Direct software No. 498925; Stat-Express software No. 498926; radio transmitter TESA BLE No. 498921 size BT; spare battery No. 445443 size AKKU; dust cover; comprehensive range of accessories (such as for measuring squareness) available on request.

Technical description

Measurement slide movement	manual
Rectangularity error (frontal)	9 µm
Repetition accuracy (2 σ)	≤ 1 µm
Error limit (L = meas. length in mm)	2 + 2L / 1000 µm
Gauging force	1.6 ±0.25 N
Weight	37 kg
Graduations can be switched over	0.01 / 0.001 / 0.0001 mm
maximum application range	0 - 770 mm
Measuring range	600 mm
Calibration	E2
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1

Power supply	Rechargeable battery-powered
Power supply	Mains operated
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	TESA Link Connector TLC
Test certificate	Manufacturer's test certificate
Type of product	Height gauge

Services

Calibration Digital height gauge maximum measuring range 800 mm	024000 800
DAkkS calibration Digital height gauge maximum measuring range 800 mm	024010 800

Accessories

Multi-receiver / USB keyboard interface Type	498975
Receiver / USB keyboard interface Type	498965
Data cable TLC, 2 m Type USB	498918 USB
USB printer for MICRO-HITE	445293
Thermal paper for USB printer	445294
Mains adapter Type MH	445282 MH