

**LED hand-held stroboscope, Type: 477****Order data**

Order number	471200 477
GTIN	4029547010651
Item class	47B

Description**Version:**

Sturdy shock-resistant casing. Extremely high measuring range up to 300,000 flashes per minute. Very high light intensity of up to 4800 Lux (LED technology). Trigger input and output permits the connection of an external system and activation by an external sensor. Battery capacity up to 5 hours.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Inspection and quality control on machines and equipment, speed measurement of objects that are inaccessible and quick-moving – without interrupting operations.

Supplied with:

Transport case, trigger signal socket, calibration certificate and 6 batteries No. 081561 size LR6.

Calibration: I2

IP Index of Protection: IP 65

Measuring range: 30 - 300000 rpm

Error limit: 0.02 (± 1 digit) %

Length: 191 mm

Width: 82 mm

Height: 60 mm

Weight: 400 g

Technical description

Height	60 mm
Width	82 mm
Weight	400 g
Length	191 mm
Operating temperature	0 - 45 °C
Measuring range	30 - 300000 rpm
Error limit	0.02 (±1 digit) %
Number of batteries contained	6
Article no of the battery / rechargeable battery fitted	081561 LR6
IP Index of Protection	IP 65
Power supply	Battery-powered
Calibration	I2
Type of product	Stroboscope

Services

Calibration Tachometer / stroboscope	016600
Labelling laser-etched Type	018940
DAkkS calibration Rotational speed sensor	016830

Accessories

Alkaline-manganese batteries International size LR6	081556 LR6
Alkaline-manganese batteries International size LR6	081561 LR6