



Digital hand-held tachometer



Order data

Order number	471100
GTIN	4029547006302
Item class	47B

Description

Version:

Non-contact measurement by reflector strip, contact measuring by means of mechanical adapter tip, memory selectable using MODE button for maximum value, minimum value, or most recent value. Switches off automatically 30 seconds after the last key action.

Application:

Rotational speed measurement:

- optical 1 to 99999 rpm non-contact,
- mechanical 0.1 to 19999 rpm with contact tip.

Speed measurement (with measuring wheel).

- 0.10 to 1999 m/min

Length measurement (with surface disc).

- 0.00 bis 99999 m

Supplied with:

Includes mechanical adapter, measuring wheel (0.1 m) No. 471180, hollow measuring tip No. 471190, drive cone centre No. 471170, measuring wheel (6 inch), reflector strips No. 471150, case, 2 batteries No. 081561 size LR6.

Technical description

Data sheet

Measurement distance (for optical measurement)	600 mm
Speed measuring range (optical)	0 - 99999 min ⁻¹
Operating temperature	0 - 50 °C
Storage temperature	-20 - 70 °C
Error limit	0.02 (±1 digit) %
#Article no of the battery / rechargeable battery fitted	081561 LR6
#Number of batteries contained	2
Power supply	Battery-powered
Reversible reading	mm / inch
Measurement technology	digital
Calibration	Price on request
Type of product	Hand-held tachometer

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/471100->
