

 Mahr

Internal micrometer for large measuring ranges, Measuring range: 100-900mm



Order data

Order number	427900 100-900
GTIN	4059192005894
Item class	43A

Description

Version:

Lightweight, kink-proof tubular construction. Measuring spindle through hardened and ground. **Measuring faces hardened and hemispherical ground.** One adjustable measuring face. Jaws, control elements, and reading parts satin chrome-plated. **Immediately ready for use without adjustment.**

Accuracy:

$(4 + L / 100) \mu\text{m}$.

Supplied with:

Micrometer, extensions No. 427950.

Optional extras:

Extensions No. 427950.

Technical description

Extension	25; 50; 100; 200; 400 mm
Barrel \varnothing	17.5 mm
Spindle \varnothing	7.5 mm
Measuring range	100 - 900 mm
Scale divisions	0.01 mm

Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S4
Type of product	2-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 100-900 mm	020480 100-900
DAkkS calibrationInternal micrometer set Measuring range 100-900 mm	020490 100-900

Accessories

Extension for internal micrometer Length 50 mm	427950 50
Extension for internal micrometer Length 800 mm	427950 800
Extension for internal micrometer Length 100 mm	427950 100
Extension for internal micrometer Length 25 mm	427950 25
Extension for internal micrometer Length 200 mm	427950 200
Extension for internal micrometer Length 400 mm	427950 400