



## High-performance cutting oil high-viscosity, chlorine-free DAR 50 Visco, Contents: 0,3l



---

### Order data

Order number	084220 0,3
GTIN	2050000966149
Item class	08J

---

### Description

#### Version:

Cutting oil for the most demanding applications. Recommended for mixing with normal mineral-based cutting oil (but not with water-soluble oils).

Application by brush, spray can, spray bottle or lubrication system.

#### Advantage:

Improves **tool-life, cutting performance** and **surface quality**. **Chlorine-free** - releases no hazardous vapours, **non-polluting**.

#### Application:

Multi-purpose for **all machining operations** (turning, milling, drilling, tapping, reaming, broaching and sawing) and also for **forming**. Indispensable when cutting **difficult materials** such as stainless and heat-resistant steels, nickel alloys, titanium, and similar alloys. Ideal for **non-ferrous metals**.

**High viscosity product** based on mineral oil, very well suited for thread tapping, good adherence.

---

### Technical description

---

Labelling of hazardous substances	GHS02: Flame
Spray head	Standard
Boiling point	-44 °C
Colour	pale yellow
hazardous goods class	2.1
Version	Spray can
Spontaneous ignition temperature	365 °C
Storage temperature	15 - 35 °C
Contents	0.3 l
Type of product	Cutting oil / grinding oil