



Measuring gauge for internal tapers IFM, Measuring range: 20-40mm



Order data

Order number	435172 20-40
GTIN	2050001055750
Item class	46D

Description

Version:

IFM internal taper measuring gauge with 90° anvil cone for **determining the largest internal taper Ø**. The hardened anvil cone cross is inserted into the internal taper. The largest Ø is determined by pressing until reaching the stop.

Supplied with:

Dial indicator.

Note:

Special versions with other taper angles available on request. Measuring devices for measuring the chamfer length available on request. Dial indicator and base body available separately.

Technical description

Measuring range	20 - 40 mm
Scale graduations	0.01 mm
Standard	DIN 878
all parts	hardened

Packaging	sturdy box
Calibration	Price on request
Type of product	Taper measuring gauge

Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30
---	-----------