



Push-pull toggle clamp with hand lever (can be pulled-out), Type: 4



Order data

Order number	376760 4
GTIN	4020772092627
Item class	35A

Description

Version:

- **Very sturdy design, with slide-ram guide.**
- **Slide-ram and hand lever move together.**
- **Body of malleable cast iron.**
- **Lever parts and slide ram made of quenched and tempered steel, galvanised and passivated.**
- **Hardened contact screw.**
- **Hardened bolts, maintenance-free sintered bushes.**
- **For high clamping forces.**
- **Body of malleable cast iron, burnished.**

Application:

- **For quick clamping / releasing in series production.**
- **As push or pull clamp.**
- **For incorporation within special jigs and fixtures.**
- **Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.**

Technical description

Weight	0.65 kg
--------	---------

Hole spacing l	36.5 mm
Hole spacing k	25 mm
Bore Ø d	5.5 mm
Clamping height b to centre of screw	12 mm
Contact screw	M8×35 mm
Base body length f	90 mm
Base body width n	47 mm
Clamping force P (pressure and traction)	7000 N
Clamping range	32 mm
Hole spacing g	33.3 mm
Overall height H	132 mm
Overall length L	155 mm
Type	6842PL
Type of product	Push-pull toggle clamp