



Engineer's precision steel rule stainless, matt finished, Length: 1000mm



Order data

| | |
|--------------|---------------|
| Order number | 461600 1000 |
| GTIN | 4045197234810 |
| Item class | 42G |

Description

Version:

Of special **stainless** clock spring steel with ground measuring edges. Wide version. Upper and lower edges both with mm graduations. Very easy to read due to matt surface and sharp graduation scale.

Graduations electrolytically etched. Matt non-reflective surface.

Technical description

| | |
|-------------------------|-----------------------|
| Cross-section width | 30 mm |
| Length | 1000 mm |
| Cross-section thickness | 1 mm |
| Calibration | F10 |
| Error limit | 0.5 mm |
| Standard | EG II |
| Material | Stainless steel, INOX |
| Type of product | Straight edge |

Services

| | |
|---|---------------|
| CalibrationSteel scale maximum length 1000/2 mm | 026200 1000/2 |
|---|---------------|