



## Digital XTL internal quick measuring set, Measuring range: 6-10mm



### Order data

Order number	428770 6-10
GTIN	5051102120528
Item class	46B

### Description

#### Version:

**3-point XT internal micrometer series** for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

#### Function:

- mm / inch selection.
- Setting 2 preset values.
- On / Off data storage button.

#### Supplied with:

Digital internal micrometers No. 428760 and setting rings with UKAS test certificate.

### Technical description

Number of measuring heads	2
Setting ring $\varnothing$	8 mm
Measuring range	6 - 10 mm

Error limit	0.004 mm
Scale divisions	0.001 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point bore gauge

## Services

CalibrationInternal micrometer set Measuring range 6-10 mm	020550 6-10
------------------------------------------------------------	-------------

## Accessories

Extension for internal micrometers Type 1/63	428510 1/63
Button cell / special battery Battery type CR2032	081560 CR2032
Setting ringDIN 2250 C Nominal size Ø 7 mm	484030 7
Setting ringDIN 2250 C Nominal size Ø 9 mm	484030 9
Connection cable Duplex Type R2	498951 R2
Connection cable Duplex Type USB2	498951 USB2