



## Digital XTL internal quick measuring device, Measuring range: 8-10mm



### Order data

Order number	428760 8-10
GTIN	2050001706416
Item class	46B

### Description

#### Version:

**3-point XT internal micrometer series** for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

#### Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

#### Supplied with:

Measuring lever, micrometer head with UKAS test certificate, 1 battery No. 081560 size CR2032.

#### Optional extras:

Data cable No. 498950 (from size 20), No. 498951 (up to size 20), setting rings No. 484030, extensions No. 428510.

### Technical description

Scale divisions	0.001 mm
Standard measuring depth	58 mm
Measuring depth with extension	121 mm
Measuring range	8 - 10 mm
Dimension a	1.9 mm
Error limit	0.004 mm

Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

## Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20

## Accessories

Extension for internal micrometers Type 1/63	428510 1/63
Setting ring DIN 2250 C Nominal size Ø 9 mm	484030 9
Button cell / special battery Battery type CR2032	081560 CR2032
Setting ring DIN 2250 C Nominal size Ø 8 mm	484030 8
Connection cable Duplex Type USB2	498951 USB2
Connection cable Duplex Type R2	498951 R2
Setting ring DIN 2250 C Nominal size Ø 10 mm	484030 10