



Digital XTL internal quick measuring set, Measuring range: 10-20mm



Order data

Order number	428770 10-20
GTIN	5051102120535
Item class	46B

Description

Version:

3-point XT internal micrometer series for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- mm / inch selection.
- Setting 2 preset values.
- On / Off data storage button.

Supplied with:

Digital internal micrometers No. 428760 and setting rings with UKAS test certificate.

Technical description

Setting ring \varnothing	12.5 / 20 mm
Measuring range	10 - 20 mm
Number of measuring heads	3

Error limit	0.004 mm
Scale divisions	0.001 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point bore gauge

Services

CalibrationInternal micrometer set Measuring range 10-20 mm	020550 10-20
---	--------------

Accessories

Extension for internal micrometers Type 2/76	428510 2/76
Button cell / special battery Battery type CR2032	081560 CR2032
Setting ringDIN 2250 C Nominal size Ø 14 mm	484030 14
Connection cable Duplex Type R2	498951 R2
Connection cable Duplex Type USB2	498951 USB2
Extension for internal micrometers Type 3/100	428510 3/100
Setting ringDIN 2250 C Nominal size Ø 11 mm	484030 11
Setting ringDIN 2250 C Nominal size Ø 18 mm	484030 18