



Digital XTL internal quick measuring device, Measuring range: 10-12,5mm



Order data

Order number	428760 10-12,5
GTIN	2050001706423
Item class	46B

Description

Version:

3-point XT internal micrometer series for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

Supplied with:

Measuring lever, micrometer head with UKAS test certificate, 1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498950 (from size 20), No. 498951 (up to size 20), setting rings No. 484030, extensions No. 428510.

Technical description

Measuring depth with extension	134 mm
Scale divisions	0.001 mm
Standard measuring depth	58 mm
Dimension a	1.9 mm
Measuring range	10 - 12.5 mm
Error limit	0.004 mm

Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

Services

Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Extension for internal micrometers Type 2/76	428510 2/76
Setting ring DIN 2250 C Nominal size Ø 11 mm	484030 11
Setting ring DIN 2250 C Nominal size Ø 10 mm	484030 10
Button cell / special battery Battery type CR2032	081560 CR2032
Connection cable Duplex Type R2	498951 R2
Setting ring DIN 2250 C Nominal size Ø 12 mm	484030 12
Connection cable Duplex Type USB2	498951 USB2