



Internal micrometer IMICRO, Measuring range: 14-17mm



Order data

Order number	428800 14-17
GTIN	7630041108095
Item class	45A

Description

Version:

Analogue 3-point internal micrometer for **high-precision measurement** of bores, even **at large depths** (can be extended with up to three extensions). Self-centring and self-aligning. Individual internal micrometer to Abbé's principle (**no first order** tilt error). Anvils titanium nitride (TIN) coated (HV5–2300).

Optional extras:

Setting rings No. 484030, extensions No. 428802.

Note:

Centring devices for large measurement depths on request.

Technical description

Standard measuring depth	77 mm
Measuring range	14 - 17 mm
Measuring depth with maximum extension	1577 mm
Dimension a	3.5 mm
Error limit	0.004 mm
Scale divisions	0.005 mm
Standard	DIN 863

Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Test certificate	Manufacturer's test certificate
Calibration	B6
Type of product	3-point internal micrometer

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20

Accessories

Extension for IMICRO internal micrometer Type 2/150	428802 2/150
Setting ring DIN 2250 C Nominal size Ø 15 mm	484030 15