



Internal micrometer IMICRO, Measuring range: 150-175mm



Order data

Order number	428800 150-175
GTIN	7630041108262
Item class	45A

Description

Version:

Analogue 3-point internal micrometer for **high-precision measurement** of bores, even **at large depths** (can be extended with up to three extensions). Self-centring and self-aligning. Individual internal micrometer to Abbé's principle (**no first order** tilt error). Anvils of titanium carbide (HV5–1300).

Optional extras:

Setting rings No. 484030, extensions No. 428802.

Note:

Centring devices for large measurement depths on request.

Technical description

Measuring range	150 - 175 mm
Standard measuring depth	81 mm
Measuring depth with maximum extension	1581 mm
Dimension a	26 mm
Error limit	0.007 mm
Scale divisions	0.01 mm
Standard	DIN 863

Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Test certificate	Manufacturer's test certificate
Calibration	B6
Type of product	3-point internal micrometer

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 200 mm	022500 200

Accessories

Setting ring DIN 2250 C Nominal size \varnothing 160 mm	484030 160
Extension for IMICRO internal micrometer Type 5/500	428802 5/500
Extension for IMICRO internal micrometer Type 5/150	428802 5/150