

Mitutoyo**Digital-analogue dial indicator 0.0005 mm reading, Measuring range: 30mm**

Order data

Order number	434651 30
GTIN	4946368500324
Item class	44A

Description

Version:

Error-free reading from large character digital display and supplementary analogue display.

Mains operated, therefore suitable for continuous measurements. Strong housing; precision bearing plunger spindle.

Function:

- **Colour changes when out of tolerance.**
- **MAX / MIN data storage.**
- **Maximum value memory (no need to search for the turning point).**
- **Zero point display, e.g. for tolerance measurements.**
- **Selectable direction of measurement.**
- **Capable of remote control and data reporting.**
- **Remote control (special accessory).**

Supplied with:

Connection cable power supply unit 220V / 9V / 500 mA.

Optional extras:

Data cable No. 498430, remote control, Digimatic Presetter.

Technical description

Calibration	C1
Gauging force	≤ 2 N
Clamping shank Ø h6	8 mm
Selectable display	0.001 / 0.0005 mm
Power supply	Mains operated
Measurement variation E MPE (measurement range)	0.0015 mm
Standard	Manufacturer's standard
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Type of product	dial gauge

Services

DAkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	023010 100
Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30

Accessories

Carbide contact point Type 18/3	434910 18/3
Steel contact point Type 11/35	434900 11/35
Steel contact point Type 14/15	434900 14/15
Extension for contact points Length L 40 mm	434920 40
Extension for contact points Length L 20 mm	434920 20
Steel contact point Type 11/20	434900 11/20
Steel contact point Type 24	434900 24
Carbide contact point Type 10	434910 10
Steel contact point Type 17	434900 17
Steel contact point Type 11/30	434900 11/30

Steel contact point Type 39	434900 39
Carbide contact point Type 16	434910 16
Steel contact point Type 14/40	434900 14/40
Extension for contact points Length L 80 mm	434920 80
Steel contact point Type 16	434900 16
Extension for contact points Length L 10 mm	434920 10
Ruby contact point Type 2	434915 2
Steel contact point Type 14/20	434900 14/20
Steel contact point Type 11	434900 11
Steel contact point Type 18/4	434900 18/4
Connecting cable Type D2	498430 D2
Steel contact point Type 14	434900 14
Steel contact point Type 13	434900 13
Extension for contact points Length L 30 mm	434920 30
Carbide contact point Type 18/4	434910 18/4
Steel contact point Type 11/25	434900 11/25
Extension for contact points Length L 50 mm	434920 50
Extension for contact points Length L 60 mm	434920 60
Extension for contact points Length L 90 mm	434920 90
Steel contact point Type 20	434900 20
Extension for contact points Length L 70 mm	434920 70
Steel contact point Type 18/3	434900 18/3
Carbide contact point Type 18/6	434910 18/6
Carbide contact point Type 2	434910 2
Steel contact point Type 30/10	434900 30/10
Carbide contact point Type 18/2	434910 18/2
Steel contact point Type 12	434900 12
Steel contact point Type 11/15	434900 11/15
Angled bracket for dial indicator 45° Clamping length 25 mm	434917 25

Steel contact point Type 28	434900 28
Carbide contact point Type 14	434910 14
Steel contact point Type 18/5	434900 18/5
Carbide contact point Type 11	434910 11
Angled bracket for dial indicator45° Clamping length 50 mm	434917 50
Connecting cable Type USB2	498430 USB2
Connecting cable Type D1	498430 D1
Angled bracket for dial indicator60° Clamping length 50 mm	434918 50
Carbide contact point Type 18/5	434910 18/5
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 14/30	434900 14/30
Steel contact point Type 2	434900 2
Steel contact point Type 15	434900 15
Steel contact point Type 10	434900 10
Extension for contact points Length L 100 mm	434920 100
Extension for contact points Length L 15 mm	434920 15
Angled bracket for dial indicator60° Clamping length 25 mm	434918 25
Carbide contact point Type 17	434910 17
Steel contact point Type 18/6	434900 18/6
Steel contact point Type 18/1	434900 18/1
Steel contact point Type 29/10	434900 29/10
Carbide contact point Type 18/1	434910 18/1
Steel contact point Type 29/20	434900 29/20
Pivoting contact point	434912