

## Garant

**Side lock arbor Form ADB with cooling channel bores, SK 40 A = 160,  
Clamping range  $\varnothing D_1$ : 12mm**



### Order data

|              |               |
|--------------|---------------|
| Order number | 300276 12     |
| GTIN         | 4045197829863 |
| Item class   | 31A           |

### Description

#### Version:

#### **GARANT –**

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

**With coolant supply holes that can be plugged.**

With Balluff/RFID chip bore.

#### **Application:**

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

#### **Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

### Technical description

|                                  |               |
|----------------------------------|---------------|
| Overhang dimension A             | 160 mm        |
| External $\varnothing D$         | 42 mm         |
| Clamping $\varnothing D_1$       | 12 mm         |
| Spare clamping screw No. 30 9900 | 12            |
| Adapter                          | SK 40 A = 160 |
| Standard                         | DIN 6359      |
| Arbor standard                   | ISO 7388-1    |
| Shape                            | ADB           |

|                                       |                     |
|---------------------------------------|---------------------|
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity                         | ≤ 3 μm              |
| Machining strategy                    | HPC                 |
| Type of product                       | Side lock arbor     |

## Accessories

|   |            |
|---|------------|
| Pull studMori-Seiki, sealed, form A suitable for steep tapers 40              | 308630 40  |
| Pull stud 45°sealed suitable for steep tapers 40                              | 308760 40  |
| Pull studForm B suitable for steep tapers 40                                  | 308640 40  |
| Pull studsealed suitable for steep tapers 40                                  | 308660 40  |
| Pull studsealed, form A suitable for steep tapers 40                          | 308610 40  |
| Pull studsealed suitable for steep tapers 40                                  | 308635 40  |
| Pull stud, 18CrNiMo7Form A suitable for steep tapers 40                       | 308605 40  |
| Pull studsealed, form B suitable for steep tapers 40                          | 308650 40  |
| Pull studMazak, form A suitable for steep tapers 40M                          | 308670 40M |
| Wrench for pull studsISO 7388 suitable for ISO taper size 40                  | 308830 40  |
| Pull stud 45°sealed suitable for steep tapers 40                              | 308765 40  |
| Pull studForm A suitable for steep tapers 40                                  | 308600 40  |
| Special pull stud with no internal threadsealed suitable for steep tapers 40  | 308700 40  |
| Pull studMori-Seiki, sealed, form A suitable for steep tapers 40              | 308625 40  |
| Special pull stud with internal thread suitable for steep tapers 40           | 308740 40  |
| Pull stud Hurco 45° with fitsealed suitable for steep tapers 40               | 308802 40  |
| Pull stud 60°sealed suitable for steep tapers 40                              | 308785 40  |
| Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40 | 308801 40  |

|  |           |
|--|-----------|
| Pull stud Hurco 90° with fitsealed suitable for steep tapers 40                          | 308806 40 |
| Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40 | 308820 40 |
| Pull stud 90°sealed suitable for steep tapers 40   | 308790 40 |
| Pull studsealed, form B suitable for steep tapers 40                                     | 308620 40 |
| Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40                          | 308615 40 |
| Pull stud 90°sealed suitable for steep tapers 40   | 308795 40 |
| Spare clamping screw for chucks with clamping Ø D1 12 mm                                 | 309900 12 |