

Garant**ER collet chuck Form ADB, SK 40 A = 130, for ER collet size: 25****Order data**

Order number	300525 25
GTIN	4045197830241
Item class	31A

Description**Version:**

Taper ground internally and externally. With Balluff/RFID chip bore.

GARANT –

- **Balancing quality G2.5 / 25,000 rpm**
- **All shanks hard turned (for smooth running!).**
- **GARANT precision clamping nut, fine balanced (G 2.5 / 25,000 rpm) and coated, giving high clamping force and low wear.**
- **Through bored.**

Application:

For clamping tools with plain shank in collets to DIN 6499 – Form A and B.

Supplied with:

Clamping nut.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS pull stud wrenches No.308820 – 308835, ER chuck key No. 309680 – 613300, ER collets No. 308901 – 309449, ER clamping nuts No. 309615 (for sealing rings), sealing rings No. 309625 – 309645 (for No. 309615).

Machining strategy: HSC

Clamping range: 1 - 16 mm

Overhang dimension A: 130 mm

External Ø D: 42 mm

Spare GARANT high-speed clamping nut No. 309610: 25

Spare HOLEX nut No. 309580: 25

Technical description

for ER collets	25
Clamping range	1 - 16 mm
Spare GARANT high-speed clamping nut No. 309610	25
External Ø D	42 mm
Spare HOLEX nut No. 309580	25
Overhang dimension A	130 mm
Clamping Ø D ₁	1-16 mm
Adapter	SK 40 A = 130
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

Accessories

ER collet set 15 pieces 2–16 mm with seal	309244
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
ER collet with seal Nominal clamping Ø d 16 mm	308959 16
ER collet Nominal clamping Ø d 12 mm	308941 12
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309409 9
Special pull stud with no internal thread sealed suitable for steep tapers 40	308720 40
ER collet Nominal clamping Ø d 2 mm	308941 2
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309409 16

Pull stud sealed, form B suitable for steep tapers 40	308650 40
ER collet Nominal clamping Ø d 3 mm	308960 3
ER collet with seal and spray nozzles Nominal clamping Ø d 10 mm	308962 10
ER collet with seal Nominal clamping Ø d 3 mm	308959 3
ER collet with seal Nominal clamping Ø d 11 mm	308959 11
ER collet with seal and spray nozzles Nominal clamping Ø d 8 mm	308962 8
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm	309447 4
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 6 mm	309413 6
ER clamping nut for HiRunER collet chucks for ER 40	309617 40
ER clamping nut High Speed for ER 25	309610 25
ER collet with seal Nominal clamping Ø d 15 mm	308946 15
ER collet Nominal clamping Ø d 8 mm	308941 8
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 12 mm	309413 12
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 7 mm	309430 7
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309411 8
ER collet with seal Nominal clamping Ø d 4 mm	308946 4
ER collet with seal Nominal clamping Ø d 8 mm	308959 8
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309411 6
Pull stud 90° sealed suitable for steep tapers 40	308790 40
ER collet with seal Nominal clamping Ø d 3 mm	308946 3
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309409 10
	309409 11

ER collet for machine taps with seal Nominal clamping Ø d 11 mm

ER collet with seal Nominal clamping Ø d 11 mm 308946 11

ER collet for machine taps with seal Nominal clamping Ø d 6 mm 309409 6

ER collet Nominal clamping Ø d 7 mm 308960 7

ER collet with seal Nominal clamping Ø d 13 mm 308946 13

ER collet for machine taps with seal and spray nozzles
Nominal clamping Ø d 8 mm 309413 8

ER collet Nominal clamping Ø d 10 mm 308960 10

ER collet with seal Nominal clamping Ø d 15 mm 308959 15

ER collet Nominal clamping Ø d 9 mm 308960 9

ET collet with radial compensation for tapping and
reaming Nominal clamping Ø d 3,5 mm 309447 3,5

ER collet for machine taps with seal Nominal clamping Ø d 12 mm 309409 12

ET collet for thread tapping, with axial compensation
Nominal clamping Ø d 10 mm 309430 10

ER collet for machine taps with seal Nominal clamping Ø d 9 mm 309411 9

ET collet for thread tapping, with axial compensation
Nominal clamping Ø d 3,5 mm 309430 3,5

ER clamping nut for ER 25 309580 25

ER collet set 15 pieces 2–16 mm 309240

ER collet Nominal clamping Ø d 16 mm 308960 16

Pull stud sealed suitable for steep tapers 40 308660 40

ER clamping nut for HiRunER collet chucks for ER 25 309617 25

ER collet Nominal clamping Ø d 6 mm 308960 6

ER collet with seal and spray nozzles Nominal clamping Ø
d 15 mm 308962 15

ER collet with seal and spray nozzles Nominal clamping Ø
d 13 mm 308962 13

ER collet Nominal clamping Ø d 9 mm 308941 9

ER collet with seal Nominal clamping Ø d 6 mm	308946 6
ER collet with seal and spray nozzles Nominal clamping Ø d 11 mm	308962 11
ER collet with seal Nominal clamping Ø d 12 mm	308959 12
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309430 2,8
ER collet set 15 pieces 2–16 mm with seal and spray nozzles	309245
ER collet Nominal clamping Ø d 7 mm	308941 7
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Pull stud Mazak, form A suitable for steep tapers 40M	308670 40M
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309411 7
ER collet with seal Nominal clamping Ø d 5 mm	308946 5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309430 4,5
ER plain bearing clamping nut for ER 25	309612 25
ER collet Nominal clamping Ø d 3 mm	308941 3
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 8 mm	309430 8
ER collet with seal Nominal clamping Ø d 12 mm	308946 12
ER collet Nominal clamping Ø d 12 mm	308960 12
ER collet with seal Nominal clamping Ø d 16 mm	308946 16
ER collet Nominal clamping Ø d 10 mm	308941 10
ER collet with seal and spray nozzles Nominal clamping Ø d 7 mm	308962 7
ER collet Nominal clamping Ø d 5 mm	308941 5
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309409 7
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 8 mm	309447 8
ER collet with seal Nominal clamping Ø d 6 mm	308959 6

Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
ER collet Nominal clamping Ø d 11 mm	308960 11
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309447 6
Pull stud sealed suitable for steep tapers 40	308635 40
ER collet with seal and spray nozzles Nominal clamping Ø d 5 mm	308962 5
ER collet with seal Nominal clamping Ø d 8 mm	308946 8
ER collet with seal and spray nozzles Nominal clamping Ø d 9 mm	308962 9
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309409 8
ER collet set 7 pieces 4–16 mm with seal	309022
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309411 4,5
ER collet with seal and spray nozzles Nominal clamping Ø d 14 mm	308962 14
ER collet Nominal clamping Ø d 13 mm	308941 13
ER collet with seal Nominal clamping Ø d 14 mm	308946 14
Pull stud Form A suitable for steep tapers 40	308600 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 9 mm	309413 9
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309409 4,5
ER collet with seal and spray nozzles Nominal clamping Ø d 6 mm	308962 6
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 7 mm	309447 7
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309411 16
ER collet with seal Nominal clamping Ø d 10 mm	308959 10

ER collet with seal Nominal clamping Ø d 5 mm	308959 5
ER chuck key for ER collet chuck 25	309680 25
ER collet Nominal clamping Ø d 8 mm	308960 8
ER collet with seal Nominal clamping Ø d 9 mm	308946 9
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 4,5 mm	309413 4,5
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm	309447 5
ER collet with seal and spray nozzles Nominal clamping Ø d 12 mm	308962 12
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309447 4,5
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
ER collet for machine taps with seal Nominal clamping Ø d 12 mm	309411 12
ER collet with seal Nominal clamping Ø d 13 mm	308959 13
ER collet for machine taps with seal Nominal clamping Ø d 14 mm	309409 14
Pull stud 60° sealed suitable for steep tapers 40	308785 40
ER collet Nominal clamping Ø d 4 mm	308960 4
ER collet Nominal clamping Ø d 15 mm	308941 15
ER collet Nominal clamping Ø d 15 mm	308960 15
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 40	308812 40
ER collet with seal Nominal clamping Ø d 14 mm	308959 14
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 40	308810 40
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
ER collet Nominal clamping Ø d 5 mm	308960 5
ER collet Nominal clamping Ø d 6 mm	308941 6
ER clamping nut for ER 40	309580 40

ER collet with seal Nominal clamping Ø d 9 mm	308959 9
ER collet Nominal clamping Ø d 14 mm	308960 14
ER clamping nut High Speed for ER 40	309610 40
ER collet for machine taps with seal Nominal clamping Ø d 11 mm	309411 11
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 11 mm	309413 11
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
ER collet Nominal clamping Ø d 2,5 mm	308941 2,5
ER collet Nominal clamping Ø d 11 mm	308941 11
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3 mm	309447 3
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 7 mm	309413 7
Special pull stud with internal thread suitable for steep tapers 40	308740 40
ER plain bearing clamping nut for ER 40	309612 40
ER collet with seal Nominal clamping Ø d 7 mm	308959 7
ER collet for machine taps with seal Nominal clamping Ø d 14 mm	309411 14
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
ER collet with seal and spray nozzles Nominal clamping Ø d 16 mm	308962 16
Pull stud sealed, form B suitable for steep tapers 40	308620 40
ER collet Nominal clamping Ø d 13 mm	308960 13
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309411 10
ER collet with seal and spray nozzles Nominal clamping Ø d 3 mm	308962 3

ER collet Nominal clamping Ø d 16 mm	308941 16
ER collet Nominal clamping Ø d 2 mm	308960 2
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
ER collet with seal Nominal clamping Ø d 7 mm	308946 7
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm	309447 10
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 10 mm	309413 10
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 9 mm	309430 9
ER collet with seal Nominal clamping Ø d 4 mm	308959 4
Pull stud Form B suitable for steep tapers 40	308640 40
ER collet with seal Nominal clamping Ø d 10 mm	308946 10
ER collet Nominal clamping Ø d 14 mm	308941 14
Torque insert for ER Mini nuts for ER collet chuck 25	309745 25
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
ER collet with seal and spray nozzles Nominal clamping Ø d 4 mm	308962 4
ER collet Nominal clamping Ø d 4 mm	308941 4
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309430 6
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 9 mm	309447 9
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 14 mm	309413 14