

**Garant**
**Carbide tipped jobber drill, uncoated, Ø DC h8: 16mm**

**Order data**

Order number	121150 16
GTIN	4045197471574
Item class	11E

**Description**
**Version:**

With carbide cutting tip. Ground between centres.  
Shank with driver tang for use in clamping collets.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**Technical description**

Number of cutting edges Z	2
Nominal Ø $D_c$	16 mm
Feed f in steel < 1100 N/mm <sup>2</sup>	0.19 mm/rev.
Flute length $L_c$	80 mm
Tolerance nominal Ø	h8
Overall length L	140 mm
Standard	DIN 8037
recommended maximum drilling depth $L_2$	56 mm
Coating	uncoated
Tool material	Carbide K20
Point angle	118 degrees
Through-coolant	no
Colour ring	without

Type of product

Jobber drill

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu > 10% Si	suitable	140 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	25 m/min	P
GG(G)	suitable	90 m/min	K
CuZn	suitable	140 m/min	N
Oil	suitable		
wet maximum	suitable		