

MT drill chuck arbor, precision version, MT / drill chuck taper: 5/18



Order data

Order number	342600 5/18
GTIN	4045197308689
Item class	33A

Description

Version:

Through hardened and ground. High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

With MT shank and tang.

The **high precision version** offers maximum concentricity and is recommended for self-tightening high-performance drill chucks No. 341000. Shanks also suitable for drill chuck taper B18 (taper \varnothing 17.431 mm): Drill chucks No. 341000, 341010 and 341250.

Application:

For mounting drill chucks on drills, lathes, jig borers etc.

Standard:

Bohrfutterkegel **DIN 238**.

Technical description

Drill chuck taper DIN 238	B 18
Morse taper MT size	5
Taper \varnothing D	17.78 mm
Type of product	Drill chuck adapter