



Feeler gauge shim roll 12.7 mm×5 m, Carbon steel, Thickness: 0,12mm



Order data

| | |
|--------------|---------------|
| Order number | 478502 0,12 |
| GTIN | 4045197519399 |
| Item class | 42H |

Description

Version:

Cold rolled, hard spring feeler strip steel of maximum precision. From size 0.02, the strip thickness is continuously marked and cannot be wiped off (exception: for No. 478502 from size 0.08).

Stored in a practical dispenser; pull out like a tape measure. The desired length can be cut from the 5 or 10 m long strip.

C-steel – Carbon steel, material No. 1.1274, cold rolled, hardened, bright surface. **(size 0.01 and 0.02 stainless).**

Application:

In jig and tool building for aligning and adjusting machine parts, as a shim for aligning components, for tolerance measurements of all kinds, for checking fits and guides, for setting up printing rollers.

Technical description

| | |
|-------------|----------------|
| Thickness | 0.12 mm |
| Error limit | ±4 µm |
| Standard | Works standard |
| Tolerance | T3 |

| | |
|-----------------|-------------------------|
| Material | Carbon steel |
| Roll length | 5 m |
| Roll width | 12.7 mm |
| Type of product | Feeler gauge shim strip |