

Garant**Tape measure with viewing window and magnetic base, Band length: 3m**

Order data

Order number	462215 3
GTIN	4045197226013
Item class	41H

Description

Version:

- **Shock-resistant plastic casing.**
- **Aluminium inlay on both work faces, giving exact contact surfaces for inside and outside measurement.**
- **Aluminium profiles resistant to heat and mechanical loads.**
- **Tape measure stove enamelled, with black characters. Cambered = non-buckling with sliding end hook (for inside and outside measurements). Sharp-contrast, abrasion-resistant rustproof scale.**
- **Graduations mm / mm (upper / lower edges).**
- **Viewing window scale reads in the same direction as the tape.**

With two strong magnets in the base.

Technical description

Tape width	16 mm
Body height	63 mm
Body length	63 mm
Body width	24 mm
Band length	3 m
Standard	EG II

Calibration	G1
Type of product	Measuring tape

Services

CalibrationTape measure maximum length 5 m	026240 5
--	----------