

**Tapered clamp with adjusting support screw, Slot width a: 10mm****Order data**

Order number	370680 10
GTIN	4020772070267
Item class	35A

Description**Version:**

Clamp painted. Clamping height steplessly adjustable via screw (without clamping lever).

Material:

Quenched and tempered steel, screw strength 8.8 or 10.9 (depending on size).

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Slot length f	30 mm
Slot width a	10 mm
Tee bolt DIN 787, No. 375300	Size 101080
Distance from tip to slot	15 mm
Clamping height h	8 - 32 mm
Length L	80 mm

Width B	30 mm
Height H	15 mm
Type	6314V
Type of product	Plain clamp