

Kroepelin
Längenmesstechnik

Internal quick caliper, Measuring range: 5-15mm



Order data

Order number	438950 5-15
GTIN	2050001661616
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Measuring range	5 - 15 mm
maximum contact point length L (measurement depth)	35 mm
Carbide spherical point \varnothing	0.6 mm
Scale divisions	0.005 mm
maximum groove depth	2.3 mm
minimum groove width	0.8 mm
Error limit	0.015 mm
Dial indicator \varnothing	65 mm
Calibration	C7

IP Index of Protection	IP 65
Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Internal quick caliper

Services

CalibrationExternal / internal quick caliper Type S	023450 S
DAkkS calibrationExternal / internal quick caliper Type S	023460 S