

**Forked clamp offset, Slot width a: 10mm****Order data**

Order number	370810 10
GTIN	4020772073183
Item class	35A

**Description****Version:**

Quenched and tempered steel, painted.

**Application:**

To achieve the **lowest clamping height, turn the clamp around.**

**Material:**

Screw strength 8.8.

**Supplied with:**

Adjusting screw and T-bolts DIN 787 (see No. 375300).

**Technical description**

Distance e from tip to end of slot	70 mm
Slot width a	10 mm
Tee bolt DIN 787, No. 375300	Size 101080
Clamping height h	8 - 37 mm
Length L	100 mm

Height H	20 mm
Width B	30 mm
Type	6315V
Type of product	Plain clamp