




Neodymium magnetic clamping block, Length: 140mm



Order data

Order number	380870 140
GTIN	4045197311313
Item class	33S

Description

Version:

- **Extremely high clamping force due to specially developed process.**
- **Sturdy all-steel body with an ON-OFF switch on the end face.**
- **Lamellae made of 2 mm brass / 4 mm steel.**
- **Neodymium magnetic system.**

Application:

- **For components which are difficult to clamp, such as Ferrotic, carbide with cobalt.**
- **For spark erosion and grinding.**

Note:

Adaptors optionally available for all zero-point clamping systems GARANT Zeroclamp on the market (Partool, 3R, Mecatool, Erowa, etc.). **Please supply the respective data when ordering.**

Technical description

Magnetic field height	4 mm
Height	51 mm
Width	70 mm
Length	140 mm
Weight	3 kg
Nominal clamping force	180 N/cm ²

Height tolerance	+0.5 / -2 mm
Type of product	Magnetic clamping plate