



Magnetic measuring stand with fine adjustment at the column, Type: N1



Order data

Order number	441190 N1
GTIN	7290005394287
Item class	46G

Description

Version:

3-point clamping of the measuring arm with very short clamping travel for high ease of use. Very low applied force generates sustained stable clamping.

Generously dimensioned frame for very high system stiffness. **Vario** dial indicator holder for shank \varnothing 6mm, 8mm, 3/8 inch, lever dial indicator with dovetail slide and dial indicators with loop at rear.

Fine adjustment at the indicator holder.

Optional extras:

Measuring microscope No. 440401.

Technical description

Column \varnothing D ₂	14 mm
Cross arm \varnothing D ₁	12 mm
Column height L ₂	203 mm
Cross arm length L ₁	185 mm

Magnetic base width	50 mm
Connection thread	M8 external thread
Magnetic base length	60 mm
Magnetic base height	55 mm
Magnetic force	800 N
Type of product	measuring stand

Accessories

Stand base Type 0	442120 0
Stand base Type V	442120 V
Stand base Type 1	442120 1
Arm clamp for universal measuring stands for column Ø of stand 12/14 mm	440351 12/14
Vario dial indicator holder Type FA1500	440401 FA1500
Stand base Type 1	442140 1
Stand base Type 0	442140 0
Stand base with fine adjustment Type 0	442125 0