



Permanent magnetic circular chuck, with radial pole distribution, Chuck Ø: 300mm



Order data

Order number	380810 300
GTIN	4045197310941
Item class	33S

Description

Version:

- **Neodymium magnet system for strong clamping force.**
- **Concentric grooves to assist component alignment.**
- **Centre is magnetically inactive, so that the plate can be bored through.**

ON-OFF control by hand-operated lever.

Application:

- **For grinding and turning.**
- **Particularly suitable for clamping annular components, due to radial pole distribution.**
- **For round and annular workpieces**

Technical description

Centre Ø	150 mm
Nominal clamping force	150 N/cm ²
Ø non-magnetic core	40 mm
Chuck Ø	300 mm

Centring hole depth	6 mm
Weight	30 kg
maximum boring-out Ø	58 mm
Thread Ø	8×M8
Pitch circle Ø	180 / 260 mm
Height tolerance	+0.5 / -2 mm
Height	73 mm
Type of product	Magnetic clamping chuck