



Permanent magnetic circular chuck, with radial pole distribution, Chuck Ø: 350mm



Order data

Order number	380810 350
GTIN	4045197310958
Item class	33S

Description

Version:

- Neodymium magnet system for strong clamping force.
- Concentric grooves to assist component alignment.
- Centre is magnetically inactive, so that the plate can be bored through.

ON-OFF control by hand-operated lever.

Application:

- For grinding and turning.
- Particularly suitable for clamping annular components, due to radial pole distribution.
- For round and annular workpieces

Technical description

Thread Ø	8×M8
Centre Ø	170 mm
Nominal clamping force	150 N/cm ²
Weight	49 kg

Centring hole depth	6 mm
Chuck Ø	350 mm
Height tolerance	+0.5 / -2 mm
Pitch circle Ø	220 / 300 mm
maximum boring-out Ø	58 mm
Ø non-magnetic core	40 mm
Height	73 mm
Type of product	Magnetic clamping chuck