



Measuring stand with fine adjustment at the magnetic base, Type: N1



Order data

Order number	441195 N1
GTIN	7290005398902
Item class	46G

Description

Version:

3-point clamping of the measuring arm with very short clamping travel for high ease of use. Very low applied force generates sustained stable clamping.

Generously dimensioned frame for very high system stiffness. **Vario** dial indicator holder for shank \varnothing 6mm, 8mm, 3/8 inch, lever dial indicator with dovetail slide and dial indicators with loop at rear.

Fine adjustment at the magnetic base. Advantage when adjusting μ m lever dial indicators, as the column is not affected by the force applied.

Optional extras:

Measuring microscope No. 440401.

Technical description

Cross arm length L_1	185 mm
Connection thread	M8 external thread
Magnetic base width	50 mm
Column \varnothing D_2	14 mm

Cross arm $\varnothing D_1$	12 mm
Magnetic force	800 N
Column height L_2	203 mm
Magnetic base height	55 mm
Magnetic base length	60 mm
Type of product	measuring stand

Accessories

Stand base Type V	442120 V
Vario dial indicator holder Type FA1410	440401 FA1410
Stand base with fine adjustment Type 0	442125 0
Stand base Type 1	442140 1
Stand base Type 0	442140 0
Stand base Type 0	442120 0
Arm clamp for universal measuring stands for column \varnothing of stand 12/14 mm	440351 12/14
Stand base Type 1	442120 1