



## Magnetic measuring stand with fine adjustment at the magnetic base, Type: 120SF



### Order data

Order number	441170 120SF
GTIN	7290005397349
Item class	46G

### Description

#### Version:

Mechanical magnetic measuring stand with central locking mechanism. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning. Magnetic base with rotary switch and Vee sole. Standard indicator holder for clamping shank  $\varnothing$  8 mm and dovetail, magnetic base with fine adjustment.

#### Callout:

##### Fine adjustment at the magnetic base

Length of jointed arm  $L_1$ : 56 mm

Length of jointed arm  $L_2$ : 51 mm

Connection thread at bottom: M5

Magnetic force: 320 N

maximum loading: 2.7 kg

Magnetic base length: 40 mm

### Technical description

Magnetic base width	30 mm
Length of jointed arm L <sub>1</sub>	56 mm
Magnetic base height	35 mm
Magnetic base length	40 mm
Throat	178 mm
Magnetic force	320 N
Length of jointed arm L <sub>2</sub>	51 mm
maximum loading	2.7 kg
Connection thread at bottom	M5
Type of product	measuring stand

## Accessories

Holder for measuring stand Type 2SM	442100 2SM
Holder for measuring stand Type QR	442100 QR
Holder for measuring stand Type K2	442100 K2
3-D jointed arm Type 120	442114 120
Vario dial indicator holder Type FA1100	440401 FA1100
Holder for measuring stand Type 2SM	442104 2SM
Stand base with fine adjustment Type S	442125 S
Stand base Type S	442140 S
Holder for measuring stand Type CA	442100 CA
3-D jointed arm Type 120	442110 120
Stand base Type S	442120 S
Holder for measuring stand Type H	442100 H
Holder for measuring stand Type K1	442100 K1