



## Stainless steel measuring tape in a capsule, Band length: 20m



### Order data

Order number	463050 20
GTIN	4007368079033
Item class	46M

### Description

**Version:**

**Capsule:** Indestructible plastic casing with soft finish surface. Storage is provided in the casing for the crank arm and the pull ring. Can be converted for left-hand use.

**Frame:** Light metal frame with ball bearing mounted fast winding and folding crank.

**Tape:** Patented tape start, **flextop coating**. Tape coating, made of transparent, highly flexible plastic, reliably prevents the tape from breaking at the start.

**Stainless tape** of hardened chromium-nickel steel, transparently enamelled. Scale printed with clear, easy-to-read figures and graduations. Break-proof, with good flexibility. With cm graduations (first 20 cm graduated in mm).

**Note:**

Versions with 100 m length, or with inch graduations, or with start of scale type B / C available on request.

### Technical description

Capsule height	32 mm
Tape width	13 mm
Capsule width	115 mm

Capsule length	138 mm
Type of tape start	A
Band length	20 m
Standard	EG II
Calibration	G1
Type of product	Measuring tape

### Services

CalibrationTape measure maximum length 50 m	026240 50
---	-----------