



## Magnetic measuring stand with fine adjustment at the magnetic base, Type: 290



### Order data

Order number	441170 290
GTIN	7290005397363
Item class	46G

### Description

#### Version:

Mechanical magnetic measuring stand with central locking mechanism. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning. Magnetic base with rotary switch and Vee sole. Standard indicator holder for clamping shank  $\varnothing$  8 mm and dovetail, magnetic base with fine adjustment.

#### Callout:

**Fine adjustment at the magnetic base**

### Technical description

Magnetic force	800 N
Magnetic base height	55 mm
Magnetic base width	50 mm
Length of jointed arm $L_1$	133 mm

Length of jointed arm L <sub>2</sub>	113 mm
maximum loading	8 kg
Throat	317 mm
Magnetic base length	60 mm
Connection thread at bottom	M8
Type of product	measuring stand

## Accessories

3-D jointed arm Type 290	442114 290
3-D jointed arm Type 290	442110 290
Holder for measuring stand Type K2	442100 K2
Stand base Type K3	442120 K3
Holder for measuring stand Type H	442100 H
Stand base Type 0	442140 0
Stand base Type 1	442120 1
Stand base Type 0	442120 0
Stand base Type V	442120 V
Stand base Type 1	442140 1
Holder for measuring stand Type QR	442100 QR
Stand base with fine adjustment Type 0	442125 0
Holder for measuring stand Type 2SM	442100 2SM
Holder for measuring stand Type CA	442100 CA
Stand base Type 1	440868 1
Holder for measuring stand Type 2SM	442104 2SM
Holder for measuring stand Type K1	442100 K1
Vario dial indicator holder Type FA1100	440401 FA1100