

**Glass fibre measuring tape in a capsule, Band length: 20m****Order data**

Order number	463300 20
GTIN	4007368072867
Item class	46M

Description**Version:**

Capsule: Indestructible plastic casing with soft finish surface. Storage is provided in the casing for the crank arm and the pull ring. Can be converted for left-hand use.

Frame: Light metal frame with ball bearing mounted fast winding and folding crank.

Glass fibre measuring tape. Extremely buckling-resistant **and flexible**, weather-proof, and resistant to many chemicals. **Electrically non-conducting.** Good legibility. With cm graduations.

Note:

Versions with 100 m length, or with inch graduations, or with start of scale type B / C available on request.

Technical description

Capsule length	175 mm
Capsule width	145 mm
Tape width	13 mm
Capsule height	32 mm
Type of tape start	A

Band length	20 m
Standard	EG II
Calibration	G1
Type of product	Measuring tape

Services

CalibrationTape measure maximum length 50 m	026240 50
---	-----------